




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	INITIAL RELEASE	04/24/2019	PHOSPODAR



Units in mm

28Gb/s SFP28 Active Optical Cable	LENGTH	
	METERS	FEET
AOCSP2825-001	1.0	3.28
AOCSP2825-003	3.0	9.84
AOCSP2825-005	5.0	16.40
AOCSP2825-007	7.0	22.97
AOCSP2825-010	10.0	32.81
AOCSP2825-020	20.0	65.62
AOCSP2825-030	30.0	98.43

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]
 OVERALL CABLE LENGTH TOLERANCE:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤60 [1524] = +2[51] / -0
 >60 [1524] ≤120 [3048] = +4 [102] / -0
 >120 [3048] ≤300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0%
 ALL OTHER DIMENSIONAL TOLERANCES:
 .X = ±.2 [5.08]
 .XX = ±.02 [5.1]
 .XXX = ±.005 [1.3]



APPROVALS	DATE
DRAWN BY DZINN	04/22/2019
CHECKED BY DFRISIELLO	04/22/2019
APPROVED BY PHOSPODAR	04/22/2019

L-com Global Connectivity
 50 HIGH STREET
 NORTH ANDOVER, MA
 01845

CATEGORY FIBER OPTICS			
PRODUCT DESCRIPTION Active Optical Cable SFP28 28Gb/s			
SIZE B	FSCM NO. 43321	DWG. NO. AOCSP2825	REV. A
SCALE: 1:4	CAD FILE AOCSP2825.SLDDRW		SHEET 1 OF 1