C C C C C C C C C C C C C C	
C CENTER PIN BRASS SILVER	D
N-MALE CONNECTOR	
	С
	₹ -
B 90[23] 94[23.9] 94[23] 9	ם
NOTES: ELECTRICAL: IMPEDANCE: 500HM FREQUENCY RANGE: DC~6 GHz INSERTION LOSS: .2 dB MAX. WORKING VOLTAGE: 2700 VRMS MAX. DIELECTRIC WITHSTANDING VOLTAGE: 4000 VRMS MIN.	
A PACKAGING: COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PKG-00012 REGULATORY COMPLIANCE: BUILD OF THE SECURE OF THE SECUR OF THE SECURE OF THE	A
ROHS, CE PROJECTION COLOR VARIATIONS SEE A3321 AXA-NMDF A 8 7 6 5 4 3 2 1	4