

6

5

4

3

2

1

REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/10/2025	DMAY	DREBECK

F

E

D


C

B

A

LENGTH (1)

LENGTH (2)



SF-81 IEC C14 MALE

B

SJT 18AWGx3C 105°C
BLACK PVC 300V VW-1

NSW28965


F082

SF-82S IEC C13 FEMALE

FILE NO. REPLACEABLE
WX(YFC-U)
PH(YFC-F)

D

2:1

FILE NO. REPLACEABLE
WX(YFC-U)
PH(YFC-F)B
2:1C
2:1

NOTES:

- VOLTAGE RATING:
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 SEC
CONDUCTOR RESISTANCE $\leq 22.84\Omega/1000m$
VOLTAGE RATING AC 300V
- CABLE MARKING:
WX(NO.441): (UL) E135710-F5 SJT 3x18AWG 105°C 300V VW-1
c(UL)SJT 3x0.824mm² (18AWG) 105°C 300V FT2
PH(NO.854): (UL) E135710-F7 SJT 3x18AWG 105°C 300V VW-1
c(UL)SJT 3x0.824mm² (18AWG) 105°C 300V FT2
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS


TOLERANCES:
X = ± 2 [5]
XX = ± 0.02 [0.5]
XXX = ± 0.005 [0.13]
FRACTIONS
 $\pm 1/32$
ANGLES $\pm 1^\circ$

CABLE LENGTH TOLERANCES:
 ≤ 12 [305] = ± 1 [25] / -0
 >12 [305] ≤ 60 [1524] = ± 2 [51] / -0
 >60 [1524] ≤ 120 [3048] = ± 4 [102] / -0
 >120 [3048] ≤ 300 [7620] = ± 6 [152] / -0
 >300 [7620] = $\pm 5\%$ / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINIT® brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE
NONE
SHEET
1 OF 2

DESCRIPTION

C14 TO C13 SPLITTER POWER CORD-10 AMP

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DMAY	C14-C132-10Y	A

6

5

4

3

2

1

6

5

4

3

2

1

F

F

E

E

D

D

C





C

B

B

A

A



CARTON LABEL

CARTON
OUTER BOX

CUSTOMER ITEM NO.	LENGTH(mm)	QTY	CARTON SIZE
C14-C132-10-10F	3048 ±30	60	50x32x28cm
C14-C132-10-15F	4572 ±30	50	50x32x28cm

L-com® an INFINIT® brand Website: www.L-com.com Phone: 1.800.341.5266 1.978.682.6936		 INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE: NONE SHEET: 2 OF 2	
DESCRIPTION C14 TO C13 SPLITTER POWER CORD-10 AMP			
SIZE A	CAGE CODE 43321	DRAWN BY DMAY	ITEM NO. C14-C132-10Y
			REV A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.

6

5

4

3

2

1