	REVISIONS		
REV	DESCRIPTION	DATE	APPROVAL
А	INITIAL RELEASE	3/11/14	D.FRISIELLO
В	ECN 7975: ADDED UV RATED, COLOR BLACK TO PE	6/4/15	D.FRISIELLO

B

CA-5EF4 HyperLink Wireless brand CAT5e.Cable

24 AWG (0.5mm) Solid Copper — Outer Jacket — PE (BLACK) Flooding Compound — Pair Insulation PE	Outdoor (UV) Rated TIA/EIA 568-B.2 ISO 11801 Flooded 4 Pair Twisted RoHS Compliant

Pair Identification

B

Pair 1	White (Blue) / Blue	
Pair 2	White (Orange) / Orange	
Pair 3	White (Green) / Green	
Pair 4	White (Brown) / Brown	

Mechanical Specification

Nominal Jacket OD	0.240"
Nominal Jacket Thickness	0.030"
Jacket Minimum Spot Thickness	0.026"
Installation Temperature 0°C to 60°C	

Electrical Performance

Frequency (MHz)	Impedance (ohm)	RL (dB)	Attenuation (dB/100m)	Next Worst Pair (dB)	Next Power Sum (dB)	ELFEXT Worst Pair (dB)	ELFEXT Power Sum (dB)	Nominal Velocity Propagation
0.772		19.4	2.2	67.0	64.0	66.0	63.0	
1.0		20.0	2.4	65.3	62.3	63.8	60.8	
4.0		23.0	4.9	56.3	53.3	51.7	48.7	
8.0] [24.5	6.9	51.8	48.8	45.7	42.7	
10.0	1 [25.0	7.8	50.3	47.3	43.8	40.8	
16.0] [25.0	9.9	47.3	44.3	39.7	36.7	
20.0	100145	25.0	11.1	45.8	42.8	37.7	34.7	0.650
25.0	100±15	24.2	12.5	44.3	41.3	35.8	32.8	0.65C
31.25		23.3	14.1	42.9	39.9	33.9	30.9	
62.5		20.7	20.4	38.4	35.4	27.8	24.8	
100		19.00	26.4	35.3	32.3	23.8	20.8	
155		17.8	31.3	32.7	29.7	18.3	17.3	
200		17.0	36.7	30.8	27.8	15.8	14.8	
250		16.3	39.5	29.3	26.3	13.8	12.8	

		APPROVALS	DATE	-			A = 1 + 1 A	
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	DRAWN BY D.FRISIELLO	3/11/14		C		Global 45 BEECHWOOD DF Connectivity NORTH ANDOVER, 1	₹IVE MA
	OVERALL CABLE LENGTH TOLERANCE:	CHECKED BY					01845	
	≤12 [305] = +1 [25] / -0	D.GUTTADAURO	3/11/14	CATEGO	RY			
	>12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0	APPROVED BY	3/11/14	0,000		-	TELECOM/MODULAR	
	>120[3048] - 300[7620] = +6 [152] / -0	D.GALLAGHER		TELECOMITMODULAR				
	>300[7620] = +5% / -0%	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUC	T DESC	RIPTION		
	ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [.51]			CA,CAT5e Series Cable				
	.XXX = .005 [.13]							
	PROJECTION _	COLOR VARI	ATIONS	SIZE	FSC/	A NO.	DWG. NO.	REV.
	(+)	MAY OCCUR		Α	43	321	CA-5EF4-R1K	В
				SCALE:	: 1:1	CAD F	ILE: CA-5EF4-R1K.SLDDRW SHEET 1 (OF 1