


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
H	ECN 7480: CHANGE HOOD DIMS, UPDATED RoHS	6/11/14	D. CASTRO



WIRING TABLE								
"P1"	PAIR	"P2"	"P1"	PAIR	"P2"	"P1"	PAIR	"P2"
1	1	1	13	13	13	25	25	25
35		35	47		47	59		59
2	2	2	14	14	14	26	26	26
36		36	48		48	60		60
3	3	3	15	15	15	27	27	27
37		37	49		49	61		61
4	4	4	16	16	16	28	28	28
38		38	50		50	62		62
5	5	5	17	17	17	29	29	29
39		39	51		51	63		63
6	6	6	18	18	18	30	30	30
40		40	52		52	64		64
7	7	7	19	19	19	31	31	31
41		41	53		53	65		65
8	8	8	20	20	20	32	32	32
42		42	54		54	66		66
9	9	9	21	21	21	33	33	33
43		43	55		55	67		67
10	10	10	22	22	22	34	34	34
44		44	56		56	68		68
11	11	11	23	23	23			
45		45	57		57			
12	12	12	24	24	24			
46		46	58		58			

DRAIN WIRE CONNECTED TO METAL FRAME OF EACH CONNECTOR

MODEL NUMBER	LENGTH	
	METERS	FEET
CA2000MM-05M	0.5	1.64
CA2000MM-1M	1.0	3.28
CA2000MM-2M	2.0	6.56
CA2000MM-3M	3.0	9.84


NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]
 OVERALL CABLE LENGTH TOLERANCE:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤60 [1524] = +2[51] / -0
 >60 [1524] ≤120 [3048] = +4 [102] / -0
 >120 [3048] ≤300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0%
 ALL OTHER DIMENSIONAL TOLERANCES:
 .X = ±.2 [5.08]
 .XX = ±.02 [5.1]
 .XXX = ±.005 [1.3]



APPROVALS	DATE
DRAWN BY D PARHAM	8/14/2001
CHECKED BY T CLARK	8/14/2001
APPROVED BY R CARRICK	8/14/2001

L-com Global Connectivity
 45 BEECHWOOD DRIVE
 NORTH ANDOVER, MA 01845

CATEGORY HETEROGENEOUS			
PRODUCT DESCRIPTION CBL,SCSI-5 .8mm CN68 M/M			
SIZE B	FSCM NO. 43321	DWG. NO. CA2000MM	REV. H
SCALE: 1:1		CAD FILE: CA2000MM.SLDDRW	SHEET 1 OF 1