


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/5/10	D.GRIFFIN
B	ECN 4906: CLARIFY PIN 1 AND ADD DIELECTRIC CALL OUT, ADDED PIN 5	7/14/10	D.FRISIELLO
C	ECN 5671: CN RELEASE	8/22/11	D.FRISIELLO
D	ECN 5868: ADDED LENGTHS 03 M, 075 M	12/8/11	D.FRISIELLO



"P1"	WIRING MAP	"P2"
1	RED	1
2	WHITE	2
3	GREEN	3
4	BLACK	4
5	BLUE	5
6	YELLOW	6
7	DRAIN WIRE	7
8	DRAIN WIRE	8
9	PURPLE	9
	ORANGE	
	BRAID	
SHELL		SHELL

MODEL NUMBER	LENGTH METERS [FEET]
CAU3AB-03M	0.3 [.98]
CAU3AB-05M	0.5 [1.64]
CAU3AB-075M	0.75 [2.46]
CAU3AB-1M	1.0 [3.28]
CAU3AB-2M	2.0 [6.56]
CAU3AB-3M	3.0 [9.84]
CAU3AB-5M	5.0 [16.41]

NOTES:

CABLE: UL STYLE 20276, 2X, TWISTED PAIR, 30AWG WITH ALUM/POLY FOIL SHIELD AND DRAIN WIRE. ONE UNSHIELDED TWISTED PAIR, 30AWG. 2 COND., 24AWG. OVERALL BRAID SHIELD, 65% JACKET: PVC, BLUE (PANTONE 300C)

MISCELLANEOUS:
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
 CABLE ASSEMBLY MUST MEET USB 3.0 REQUIREMENTS.
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY M.MARTINEZ APPROVED BY S.SMITH	DATE 4/2/10 4/2/10 4/2/10	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY USB 3.0	
	PRODUCT DESCRIPTION CA, USB 3.0 TYPE A-M TO TYPE B-M		SIZE A	FSCM NO. 43321
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	DWG. NO. CAU3AB	REV. D
SCALE: NONE		CAD FILE: CAU3AB.SLDDRW	SHEET 1 OF 1	