






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/15/2023	DFRISIELLO	GUTTADAURO



USB3.0 UL2725  
2 PAIR, STRANDED TINNED COPPER,  
INDIVIDUALLY SHIELDED WITH DRAIN WIRE  
1 PAIR, STRANDED TINNED COPPER, UNSHIELDED  
2 COND. STRANDED TINNED COPPER  
WITH OVERALL ALUM/POLY SHIELD AND DRAIN WIRE  
JACKET: PVC, BLACK



**PIN Assignment**



ITEM NUMBER	LENGTH, FT [mm]	TOLERANCE, IN [mm]
CAU3ACEXT-MF-5M	16.41 [5000.0]	±1.97 [50.0]

NOTES:  
PASS: 5Gbps/2A 5V TEST

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DFRISIELLO	05/15/2023	
CHECKED BY RCARLESKO	05/15/2023	PRODUCT DESCRIPTION USB 3.0 EXTENSION, AM/CF, SINGLE CONNECTOR	
APPROVED BY GUTTADAURO	05/15/2023	SIZE A	CAGE CODE 43321
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	ITEM NO. CAU3ACEXT-MF	REV. A
SCALE: NONE		CAD FILE: CAU3ACEXT-MF.SLDDRW	
		SHEET 1 OF 1	