






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/30/2022	GUTTADAURO





UL STYLE 20276, USB3.0 HIGH FLEX CABLE,  
(2) TWISTED PAIR, 28AWG WITH ALUM/POLY,  
DRAIN WIRE AND SPIRAL SHIELD, (1) UNSHIELDED  
TWISTED PAIR, 26AWG, (1) UNSHIELDED TWISTED  
PAIR, 22AWG, OVERALL ALUM/POLY AND BRAIDED  
SHIELD, JACKET: PVC, BLACK (NOM DIA. .276"  
[7.0]; FLAME RATING: UL VW-1; MIN. FIXED BEND  
RADIUS: 5X O.D.; MIN. MOVING BEND RADIUS: 10X  
O.D. )

PART NUMBER	LENGTH METERS [FEET]
CAU3HFA-90DB-05M	0.5 [1.64]
CAU3HFA-90DB-1M	1.0 [3.28]
CAU3HFA-90DB-105M	1.5 [4.92]
CAU3HFA-90DB-2M	2.0 [6.56]
CAU3HFA-90DB-205M	2.5 [8.20]

NOTES:

1. CABLE TYPE-U DRAG CHAIN TESTING:  
5 MILLION CYCLES MIN. (75mm BEND RADIUS)
2. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
3. CABLE ASSEMBLY SHALL MEET USB 3.0 REQUIREMENTS.
4. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
5. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS	DATE	 an INFINITO® brand	80 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936			
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY SLI	01/19/2022		CATEGORY USB			
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]		CHECKED BY GUTTADAURO	01/19/2022	PRODUCT DESCRIPTION CA HI-FLEX USB3.0 A/90DN B				
THIRD-ANGLE PROJECTION 		APPROVED BY GUTTADAURO	01/19/2022	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	CAGE CODE 43321	DWG. NO. CAU3HFA-90DB	REV. A
SCALE: NONE		CAD FILE: CAU3HFA-90DB.SLDRW		SHEET 1 OF 1				