





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/18/2022	GUTTADAURO





.463  
[11.75]  
MIN



UL STYLE 20276, USB3.0 HIGH FLEX CABLE, (2) TWISTED PAIR, 28AWG WITH ALUM/POLY, DRAIN WIRE AND SPIRAL SHIELD, (1) UNSHIELDED TWISTED PAIR, 26AWG, (1) UNSHIELDED TWISTED PAIR, 22AWG, OVERALL ALUM/POLY AND BRAIDED SHIELD, JACKET: PVC, BLACK (NOM DIA. .276" [7.0]; FLAME RATING: UL VW-1; MIN. FIXED BEND RADIUS: 5X O.D.; MIN. MOVING BEND RADIUS: 10X O.D. )

PART NUMBER	LENGTH METERS [FEET]
CAU3HFA-90DMB-05M	0.5 [1.64]
CAU3HFA-90DMB-1M	1.0 [3.28]
CAU3HFA-90DMB-105M	1.5 [4.92]
CAU3HFA-90DMB-2M	2.0 [6.56]
CAU3HFA-90DMB-205M	2.5 [8.20]

- NOTES:**
- CABLE TYPE-U DRAG CHAIN TESTING: 5 MILLION CYCLES MIN.(75mm BEND RADIUS)
  - CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936				
	DRAWN BY SLI	01/18/2022					
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	CHECKED BY GUTTADAURO	01/18/2022	CATEGORY <b>USB</b>				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [.13]	APPROVED BY GUTTADAURO	01/18/2022	PRODUCT DESCRIPTION <b>CA HI-FLEX USB3.0 A/90DN MICB</b>				
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	<table border="1"> <tr> <td>SIZE <b>A</b></td> <td>CAGE CODE <b>43321</b></td> <td>DWG. NO. <b>CAU3HFA-90DMB</b></td> <td>REV. <b>A</b></td> </tr> </table>	SIZE <b>A</b>	CAGE CODE <b>43321</b>	DWG. NO. <b>CAU3HFA-90DMB</b>	REV. <b>A</b>
SIZE <b>A</b>	CAGE CODE <b>43321</b>	DWG. NO. <b>CAU3HFA-90DMB</b>	REV. <b>A</b>				
SCALE: NONE		CAD FILE: CAU3HFA-90DMB.SLDRW	SHEET 1 OF 1				