



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	PRELIMINARY RELEASE	09/02/2022	GUITADAURO



UL STYLE 20276, USB3.0 HIGH FLEX CABLE,
 (2) TWISTED PAIR, 28AWG WITH ALUM/POLY, DRAIN WIRE AND SPIRAL SHIELD,
 (1) UNSHIELDED TWISTED PAIR, 26AWG,
 (1) UNSHIELDED TWISTED PAIR, 22AWG,
 OVERALL ALUM/POLY AND BRAIDED SHIELD,
 JACKET: PVC, BLACK
 (NOM DIA. .276" [7.0]); FLAME RATING: UL VW-1;
 MIN. FIXED BEND RADIUS: 5X O.D.;
 MIN. MOVING BEND RADIUS: 10X O.D.)

PART NUMBER	LENGTH METERS [FEET]
CAU3HFA-90RA-05M	0.5 [1.64]
CAU3HFA-90RA-1M	1.0 [3.28]
CAU3HFA-90RA-105M	1.5 [4.92]
CAU3HFA-90RA-2M	2.0 [6.56]
CAU3HFA-90RA-205M	2.5 [8.20]

- NOTES:**
- CABLE TYPE-U DRAG CHAIN TESTING: 5 MILLION CYCLES MIN.(75mm BEND RADIUS)
 - CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
 - CABLE ASSEMBLY SHALL MEET USB 3.0 REQUIREMENTS.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS SLI	DATE 01/21/2022	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CHECKED BY GUITADAURO	01/21/2022	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION CA HI-FLEX USB3.0 A/90RT A	
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	DWG. NO. CAU3HFA-90RA
SCALE: NONE		CAD FILE: CAU3HFA-90RA.SLDDRW	REV. A