



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |            |            |
|-----------|-----------------|------------|------------|
| REV       | DESCRIPTION     | DATE       | APPROVED   |
| A         | INITIAL RELEASE | 08/18/2022 | GUTTADAURO |
|           |                 |            |            |
|           |                 |            |            |



| PART NUMBER         | LENGTH METERS [FEET] |
|---------------------|----------------------|
| CAU3HFA-90UMBV-05M  | 0.5 [1.64]           |
| CAU3HFA-90UMBV-1M   | 1.0 [3.28]           |
| CAU3HFA-90UMBV-105M | 1.5 [4.92]           |
| CAU3HFA-90UMBV-2M   | 2.0 [6.56]           |
| CAU3HFA-90UMBV-205M | 2.5 [8.20]           |

- NOTES:**
1. CABLE TYPE-U DRAG CHAIN TESTING: 5 MILLION CYCLES MIN.(75mm BEND RADIUS)
  2. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
  3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

|   |  |                                   |  |                  |                           |                                   |                  |
|---|--|-----------------------------------|--|------------------|---------------------------|-----------------------------------|------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]   | APPROVALS  | DATE                              | <br>50 High Street, West Mill,<br>North Andover, MA 01845 USA.<br>Phone: 1.800.341.5266<br>1.978.682.6936 |                  |                           |                                   |                  |
|   | DRAWN BY<br>SLI  | 01/24/2022                        |  |                  |                           |                                   |                  |
| OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0 | CHECKED BY<br>GUTTADAURO                                 | 01/24/2022                        | CATEGORY<br>USB  |                  |                           |                                   |                  |
| ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2 [5]   FRACTIONS ± 1/32<br>.XX = ± .02 [.5]   ANGLES ± 1°<br>.XXX = ± .005 [.13]  | APPROVED BY<br>GUTTADAURO                                | 01/24/2022                        | PRODUCT DESCRIPTION<br>CA HI-FLEX USB3.0 A/90UP MICB W/ HDW  |                  |                           |                                   |                  |
| THIRD-ANGLE PROJECTION  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | COLOR VARIATIONS MAY OCCUR        | <table border="1"> <tr> <td>SIZE<br/><b>A</b></td> <td>CAGE CODE<br/><b>43321</b></td> <td>DWG. NO.<br/><b>CAU3HFA-90UMBV</b></td> <td>REV.<br/><b>A</b></td> </tr> </table>                   | SIZE<br><b>A</b> | CAGE CODE<br><b>43321</b> | DWG. NO.<br><b>CAU3HFA-90UMBV</b> | REV.<br><b>A</b> |
| SIZE<br><b>A</b>  | CAGE CODE<br><b>43321</b>                                | DWG. NO.<br><b>CAU3HFA-90UMBV</b> | REV.<br><b>A</b>   |                  |                           |                                   |                  |
| SCALE: NONE   |  | CAD FILE: CAU3HFA-90UMBV.SLDDRW   | SHEET 1 OF 1   |                  |                           |                                   |                  |