



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/14/2022	GUTTADAURO

.27±.01 [6.8±0.2] LENGTH .27±.01 [6.8±0.2]



P1
USB TYPE C MALE
CONNECTOR

P2
16 PIN MALE
LIGHTNING
CONNECTOR

3 CONDUCTOR 30AWG STRANDED TINNED COPPER
2 CONDUCTOR 24AWG STRANDED TINNED COPPER
JACKET: TPE 80A, WHITE NOM. O.D.: .126" [3.2]

P1 WIRING P2
 MAP

GND	Black	GND
CC	Yellow	CC
D+	Green	D+
D-	White	D-
V+	Red	V+



ITEM NUMBER	LENGTH FT [MM]
CAUC-LT-WHT-1F	1.0 [304.8 +51/-0]
CAUC-LT-WHT-2F	2.0 [609.6 +51/-0]
CAUC-LT-WHT-3F	3.0 [914.4 +51/-0]

NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DFRISIELLO	01/14/2022	
THIRD-ANGLE PROJECTION 	CHECKED BY DGUST	01/14/2022	CATEGORY AUDIO/VIDEO
	APPROVED BY GUTTADAURO	01/14/2022	PRODUCT DESCRIPTION USB C to Lightning Assembly, M/M, WHT
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321
		ITEM NO. CAUC-LT-WHT	REV. A
		SCALE: NONE	CAD FILE: CAUC-LT-WHT.SLDDRW
		SHEET 1 OF 1	