


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
D	ECN 6436: UPDATED LOGOS, DRAWING FORMAT, PACKAGING	9/28/12	D. DESJARDIN



PART NUMBER	LENGTH FEET [METERS]
CC58C-1HR2	1.0 [.30]
CC58C-1.5HR2	1.5 [.46]
CC58C-2HR2	2.0 [.61]
CC58C-2.5HR2	2.5 [.76]
CC58C-3HR2	3.0 [.91]
CC58C-4HR2	4.0 [1.22]
CC58C-5HR2	5.0 [1.52]
CC58C-7.5HR2	7.5 [2.28]
CC58C-10HR2	10.0 [3.05]
CC58C-15HR2	15.0 [4.57]
CC58C-20HR2	20.0 [6.09]

NOTES:

- CABLE SHALL BE TESTED FOR CONTINUITY.
- CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY MCCORMICK CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 05/07/01 06/06/01 06/08/01	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
		DWG. NO. CC58C-HR2	REV. D
		SCALE: NONE	CAD FILE: CC58C-HR2.SLDDRW
		SHEET 1 OF 1	