


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 3779: DEFINED COLOR TO LIGHT GRAY, NEW FORMAT	1/7/09	D.FRISIELLO
F	ECN 4474: ADDED 1.0 FT. LENGTH, UPDATED FORMAT, ADDED NOTES	1/7/10	D. CASTRO
G	ECN 6603: REVISED L-COM LOGO, ADDED COLOR	1/25/13	D.FRISIELLO



2X, 15-PIN MALE D-SUB CONNECTOR GOLD PLATED PINS

WIRING MAP		
"P1"	WIRE COLOR	"P2"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	PURPLE	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK / WHITE	13
14	BROWN / WHITE	14
15	RED / WHITE	15
SHELL	DRAIN WIRE	SHELL

2X, MOLDED PVC STRAIN RELIEF AND HOOD WITH 360° METAL FOIL SHIELD COLOR: LIGHT GRAY (PANTONE 400C)

PART NUMBER	LENGTH	
	FEET	METERS
CSMN15MM-1	1	0.31
CSMN15MM-2.5	2.5	0.76
CSMN15MM-5	5	1.52
CSMN15MM-10	10	3.05
CSMN15MM-15	15	4.57
CSMN15MM-25	25	7.62
CSMN15MM-50	50	15.24

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY: TJC CHECKED BY: DFP APPROVED BY: CM	DATE 6/7/01 7/18/01 7/19/01	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY D-SUBMINIATURE	
	PROJECTION 	COLOR VARIATIONS MAY OCCUR CSMN-FS01	PRODUCT DESCRIPTION DELUXE MOLDED CABLE, DB15M TO DB15M	SIZE A
	FSCM NO. 43321	DWG. NO. CSMN15MM	REV. G	

SCALE: NONE CAD FILE: CSMN15MM.SLDDRW SHEET 1 OF 1