


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/26/13	D.GRIFFIN
B	ECN 7592: ADD TRIANGEL POCKETS ON HOOD, UPT ROHS NOTE	9/9/14	S.LI



"P1"	WIRE COLOR	"J1"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	VIOLET	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	PINK/BLACK	12
13	LIGHT GREEN	13
14	BLACK/WHITE	14
15	BROWN/WHITE	15
16	RED/WHITE	16
17	ORANGE/WHITE	17
18	GREEN/WHITE	18
19	BLUE/WHITE	19
20	VIOLET/WHITE	20
21	RED/BLACK	21
22	ORANGE/BLACK	22
23	YELLOW/BLACK	23
24	GREEN/BLACK	24
25	GRAY/BLACK	25
SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FT	METERS
CSPL25MF-2.5	2.5	0.76
CSPL25MF-5	5.0	1.52
CSPL25MF-10	10.0	3.05
CSPL25MF-15	15.0	4.57
CSPL25MF-25	25.0	7.62
CSPL25MF-50	50.0	15.24

NOTES:

- CABLE: U.L. STYLE 2919 TYPE CL2, 25 CONDUCTOR (26AWG) (DOUBLE SHIELDED, BRAID & FOIL) JACKET: PVC, COLOR: LIGHT GRAY (PANTONE 400C)
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005 PROJECTION 	APPROVALS DRAWN BY D.PARHAM CHECKED BY D.DESJARDIN APPROVED BY S.SMITH	DATE 05/06/11 01/04/2013 01/04/2013	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CATEGORY D-SUBMINIATURE		PRODUCT DESCRIPTION CA DB25M/F PLAS ARMR
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		
	SIZE A	FSCM NO. 43321	DWG. NO. CSPL25MF

SCALE: NONE CAD FILE: CSPL25MF.SLDDRW SHEET 1 OF 1