


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/29/2020	GUTTADAURO





ITEM NUMBER	TYPE	DATA RATE	CONNECTOR TYPE	CABLE TYPE	CODING	LENGTH	
DAC-A10GMSA-3M	Active	10gig	SFP+	Twinax	MSA	9.84ft	3m
DAC-A10GMSA-5M	Active	10gig	SFP+	Twinax	MSA	16.40ft	5m
DAC-A10GMSA-7M	Active	10gig	SFP+	Twinax	MSA	22.97ft	7m
DAC-A10GMSA-10M	Active	10gig	SFP+	Twinax	MSA	32.81ft	10m

NOTES:

- 1a. STORAGE TEMP: -40°C MIN TO +85°C MAX.
- 1b. OPERATING CASE TEMP: -5°C MIN TO +75°C MAX.
- 1c. WATTAGE: 0.35W.
- 1d. POWER SUPPLY VOLTAGE (Vcc): 3.14V MIN, 3.3V TYP., 3.47V MAX.
- 1e. POWER SUPPLY CURRENT (Icc) 100mA.
- 1f. TOTAL POWER CONSUMPTION(Pd): 0.5W.

2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY DZINN	DATE 06/29/2020	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CHECKED BY DFRISIELLO	DATE 06/29/2020	
THIRD-ANGLE PROJECTION 	APPROVED BY GUTTADAURO	DATE 06/29/2020	PRODUCT DESCRIPTION DAC Cable, Active, 10Gig, SFP+/SFP+, MSA
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR	SCALE: NONE CAD FILE: DAC-A10GMSA.SLDDRW SHEET 1 OF 1
SIZE <b>A</b>		CAGE CODE <b>43321</b>	ITEM NO. DAC-A10GMSA REV. <b>A</b>