



REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	06/10/2025	DMAY	DGUTTADAURO


F




P1
DP20P M PLUG
GOLD PLATED



CABLE [1P*30#(7/0.10TCID:0.78MM-FM-PE)+D(7/0.10TCID:0.55HDPE)+ AL]*5P+5C*30#(7/0.10TCID:0.55HD-PE)+ AL+F+D(7/0.10BC)+B(80/0.12AM)
JACKET: OD:6.0±0.15MM BLACK PVC



P2
DP20P M PLUG
DOWN ANGLE
GOLD PLATED



ITEM NUMBER	LENGTH	
	[mm]	[in]
DP8DA-MM-1M	1000±20	39.37±.8
DP8DA-MM-3M	3000±30	118.1±1.2

NOTES:

1. ELECTRICAL TEST: PASS 8K@60Hz TEST.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5] FRACTIONS
XX = ±.02 [0.5] ± 1/32
XXX = ±.005 [0.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = ±1 [25] / -0
>12 [305] ≤ 60 [1524] = ±2 [51] / -0
>60 [1524] ≤ 120 [3048] = ±4 [102] / -0
>120 [3048] ≤ 300 [7620] = ±6 [152] / -0
>300 [7620] = ±5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE® brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5
SCALE SHEET
NONE 1 OF 1

DESCRIPTION
DISPLAYPORT CABLE, MALE TO DOWN ANGLE MALE, 8K
RESOLUTION

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DMAY	DP8DA-MM	A