



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN 11696: ADD RATING TEMPERATURE NOTE	2/21/22	DGUST



DIMENSIONS ARE METRIC

PART NUMBER	LENGTH METER [FEET]
DPA00006-05M	.5 [1.64]
DPA00006-1M	1.0 [3.28]
DPA00006-2M	2.0 [6.56]
DPA00006-3M	3.0 [9.84]





NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY. NO OPENS/SHORTS, MISWIRING OR INTERMITTENT FAILURES.

VOLTAGE TEST: DC 300V 10MS
 INSULATION RESISTANCE: 5.0M OHM / MIN.
 CONDUCTOR RESISTANCE: 5.0 OHM / MAX.
 RATING: TEMPERATURE 80 °C

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS B.PUCHAASKI	DATE 05/21/18	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CHECKED BY J.LABOY	DATE 05/21/18	
THIRD-ANGLE PROJECTION 	APPROVED BY B.GATES	DATE 05/21/18	PRODUCT DESCRIPTION DISPLAYPORT CABLE 20 PIN
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321
SCALE: NONE	CAD FILE: DPA00006.SLDDRW	ITEM NO. DISPLAYPORT CABLE 20 PIN	REV. B