



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	3/2/2023	DMAY	DGUTTADAURO





PART NUMBER	LENGTH	
	FEET	METERS
DPHDMI-MM-05M	1.64	0.5 ± .02
DPHDMI-MM-1M	3.28	1.0 ± .03
DPHDMI-MM-2M	6.56	2.0 ± .03
DPHDMI-MM-3M	9.84	3.0 ± .03

NOTES:

- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	08/09/2022	
CHECKED BY HBAKKE	8/30/2022	PRODUCT DESCRIPTION DP TO HDMI 2.0 M/M, 4K NYLON BRAIDED CABLE	
APPROVED BY DGUTTADAURO	8/30/2022	SIZE A	CAGE CODE 43321
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	ITEM NO. DPHDMI-MM	REV. A
SCALE: NONE		CAD FILE: DPHDMI-MM.SLDDRW	SHEET 1 OF 1