



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



| REVISION | | | | | |
|----------|-----|-----------------|----------|------------|-------------|
| ZONE | REV | DESCRIPTION | DATE | CHANGED BY | APPROVED |
| | A | INITIAL RELEASE | 3/2/2023 | DMAY | DGUTTADAURO |



| PART NUMBER | LENGTH | |
|--------------|--------|-----------|
| | FEET | METERS |
| DPMDP-MM-05M | 1.64 | 0.5 ± .02 |
| DPMDP-MM-1M | 3.28 | 1.0 ± .03 |
| DPMDP-MM-2M | 6.56 | 2.0 ± .03 |
| DPMDP-MM-3M | 9.84 | 3.0 ± .03 |

- NOTES:
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL, APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

| | | | |
|--|--|----------|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13] | APPROVALS | DATE |  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 |
| | DRAWN BY DMAY | 3/2/2023 | |
| THIRD-ANGLE PROJECTION  | CHECKED BY HBAKKE | 3/3/2023 | PRODUCT DESCRIPTION DISPLAYPORT TO MINI DISPLAYPORT M/M, 4K, NYLON BRAIDED CABLE |
| | APPROVED BY DGUTTADAURO | 3/3/2023 | SIZE A |
| | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | CAGE CODE 43321 |
| | COLOR VARIATIONS MAY OCCUR | | ITEM NO. DPMDP-MM |
| | | | SCALE: NONE |
| | | | CAD FILE: DPMDP-MM.SLDRW |
| | | | SHEET 1 OF 1 |