




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	3/2/2023	DMAY	DGUTTADAURO




P1
MDP/M
SHELL/PIN: GOLD PLATED



P2
DP/M
SHELL/PIN: GOLD PLATED



UL20276 (7/0.08TC*1P+D7/0.08TC+AL-FOIL)*5P+7/0.08TC*4C +7/0.12TC*1C+AL-FOIL+D1/0.20TC+B112/012AM, JACKET: BLACK PVC OD5.2 +BLACK THREE WIRE NYLON NET OD: 6.0±0.15mm



PART NUMBER	LENGTH	
	FEET	METERS
DPMDP-MM-05M	1.64	0.5 ± .02
DPMDP-MM-1M	3.28	1.0 ± .03
DPMDP-MM-2M	6.56	2.0 ± .03
DPMDP-MM-3M	9.84	3.0 ± .03

- NOTES:
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL, APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	3/2/2023	
THIRD-ANGLE PROJECTION	CHECKED BY HBAKKE	3/3/2023	PRODUCT DESCRIPTION DISPLAYPORT TO MINI DISPLAYPORT M/M, 4K, NYLON BRAIDED CABLE
	APPROVED BY DGUTTADAURO	3/3/2023	SIZE: A CAGE CODE: 43321 ITEM NO.: DPMDP-MM SCALE: NONE CAD FILE: DPMDP-MM.SLDRW
COLOR VARIATIONS MAY OCCUR		SHEET 1 OF 1	