



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/30/2022	DGUITADAURO



PART NUMBER	LENGTH	
	FEET	METERS
DPMDP-MM-F-05M	1.64	0.5 ± .02
DPMDP-MM-F-1M	3.28	1.0 ± .03
DPMDP-MM-F-2M	6.56	2.0 ± .03
DPMDP-MM-F-3M	9.84	3.0 ± .03

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY DMAY	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [5]      ANGLES ± 1° .XXX = ± .005 [13]	CHECKED BY HBAKKE	8/30/2022	CATEGORY  AUDIO/VIDEO
	APPROVED BY DGUITADAURO	8/30/2022	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION DISPLAYPORT TO MINI DISPLAYPORT MALE TO MALE W/ FERRITES, 4K	SIZE <b>A</b>
COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAGE CODE <b>43321</b>	ITEM NO. DPMDP-MM-F
SHEET 1 OF 1	CAD FILE: DPMDP-MM-F.SLDDRW	REV. <b>A</b>	SHEET 1 OF 1