



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/17/11	D.GRIFFIN
B	ECN8182; UPT DWG FROM MOLDED THUMBSCREW TO METAL THUMBSCREW	11/30/2015	B.ZHANG
C	ECN_8257; CHANGE DVI ICON TO THE RIGHT ORIENTATION	2/18/2016	B.ZHANG
D	ECN 9038; CHANGE ENCAPSULATED FERRITE BEAD FROM MTN-228 TO MTN-286	01/03/2018	B.ZHANG



"P1"	WIRE MAP	"P2"
19	[Wiring Diagram]	19 (GND)
18		18 (LT. GREEN)
17		17 (BLACK)
10	[Wiring Diagram]	10 (YELLOW)
9		9 (BROWN)
11		11 (GND)
15	[Wiring Diagram]	15 (BLACK)
14		14 (BROWN)
2	[Wiring Diagram]	2 (RED)
1		1 (ORANGE)
3		3 (GND)
22	[Wiring Diagram]	22 (GND)
23		23 (LT. BLUE)
24		24 (WHITE)
16	[Wiring Diagram]	16 (ORANGE)
7		7 (YELLOW)
6		6 (WHITE)
SHELL		SHELL (SHIELD DRAIN WIRE)

PIN 8 NO CONNECTION

PART NUMBER	LENGTH	
	METERS	[FEET]
DVIDS-RA-0.5M	0.5	[1.64]
DVIDS-RA-1M	1.0	[3.28]
DVIDS-RA-2M	2.0	[6.56]
DVIDS-RA-3M	3.0	[9.84]
DVIDS-RA-4M	4.0	[13.12]
DVIDS-RA-5M	5.0	[16.41]

- NOTES:**
- CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY
 - CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.
 - DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [1524] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY D. CASTRO CHECKED BY D. PARHAM APPROVED BY P. MCNEIL	DATE 11/17/11 11/17/11 11/17/11	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY AUDIO/VIDEO
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	PRODUCT DESCRIPTION CBL DVI-D SL RA
	REF	SCALE: NONE	FSCM NO. 43321	DWG. NO. DVIDS-RA-M
		CAD FILE: DVIDS-RA-M.SLDDRW	REV. D SHEET 1 OF 1	