



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 9038; CHANGE ENCAPSULATED FERRITE BEAD FROM MTN-288 TO MTN-284	01/03/2018	B.ZHANG
F	ECN 10829; REVISE UL STYLE TO 21551, ADD LSZH CBL CHARACTERISTICS TO DWG, NEW FORMAT	12/10/2020	M.BLACKWOOD



PART NUMBER	LENGTH	
	FEET	METERS
DVIDS-RA2Z-1	1.0	[.30]
DVIDS-RA2Z-3	3.0	[.91]
DVIDS-RA2Z-5	5.0	[1.52]
DVIDS-RA2Z-10	10.0	[3.05]
DVIDS-RA2Z-15	15.0	[4.57]

LSZH CABLE CHARACTERISTICS:

FLAME RATING: IEC 60332-1
 CORROSIVE GAS: IEC 60754
 SMOKE EMISSION: IEC 61034

- NOTES:**
- CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY
 - CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.
 - DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ± 1/32 .XXX = ± .005 [13] ANGLES ± 1°	APPROVALS DRAWN BY: D. PARHAM CHECKED BY: D. FRISIELLO APPROVED BY: P. McNEIL	DATE 12/16/2011 12/16/2011 12/16/2011	 an INFINITI brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY AUDIO/VIDEO	
THIRD-ANGLE PROJECTION 	REF	SIZE A CAGE CODE 43321 DWG. NO. DVIDS-RA2Z	REV. F SCALE: NONE CAD FILE: DVIDS-RA2Z.SLDDRW SHEET 1 OF 1