

6

5

4

3

2

1

REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	02/13/2026	DMAY	DGUTTADAURO

F

E

D

C

B

A

F


E

D




C

B

A



RECOMMENDED
PANEL OPENING



KIT SHOWN FULLY ASSEMBLED FOR CLARITY
(KIT IS SHIPPED UN-ASSEMBLED)

KIT INCLUDES:

- 1-UNSHIELDED ADAPTER
- 1-FLANGE ADAPTER
- 1-PACKAGE MOUNTING SCREWS (4-40x 1/4")

NOTES:

MATERIAL:

FLANGED ADAPTER: ZINC ALLOY

HARDWARE: STAINLESS STEEL.

FINISH:

FLANGED ADAPTER: NICKEL PLATE.

MISCELLANEOUS:

OPERATING TEMPERATURE: -10°C TO 60°C.

IDC: SUITABLE FOR 23-26AWG STRANDED AND SOLID WIRE.



MIN. 20-INSTALLATION CYCLES.

PACKAGING:

KIT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE
WITH L-COM PACKAGING SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).



CAT 6, UNSHIELDED
KEYSTONE ADAPTER
(L-COM P/N: RJSBTLC6-BLK
WITHOUT PACKAGING)

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:	
X = ±.2 [5]	FRACTIONS ± 1/32
.XX = ±.02 [0.5]	ANGLES ± 1°
.XXX = ±.005 [0.13]	

CABLE LENGTH TOLERANCES:	
≤12 [305]	±.1 [25] / -0
>12 [305] ≤ 60 [1524]	±.2 [51] / -0
>60 [1524] ≤ 120 [3048]	±.4 [102] / -0
>120 [3048] ≤ 300 [7620]	±.6 [152] / -0
>300 [7620]	±.5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINIT® brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE	SHEET
NONE	1 OF 1

DESCRIPTION
ETHERNET CATEGORY 6 ULTRA SHORT-BODY TOOL-LESS IDC
KEYSTONE JACK PANEL MOUNT FLANGE STYLE KIT, RJ45,
UNSHIELDED, BLACK

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DMAY	ECFRJSBTLC6-BLK	A

6

5

4

3

2

1