

6

5

4

3

2

1

REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	02/13/2026	DMAY	DGUTTADAURO

F

E

D

C

B

A

F


E

D



C

B

A



RECOMMENDED
PANEL OPENING





KIT SHOWN FULLY ASSEMBLED FOR CLARITY
(KIT IS SHIPPED UN-ASSEMBLED)

KIT INCLUDES:
1-UNSHIELDED ADAPTER
1-FLANGE ADAPTER
1-PACKAGE MOUNTING SCREWS (4-40x 1/4")

NOTES:
MATERIAL:
FLANGED ADAPTER: ZINC ALLOY
HARDWARE: STAINLESS STEEL.
FINISH:
FLANGED ADAPTER: NICKEL PLATE.
MISCELLANEOUS:
OPERATING TEMPERATURE: -10°C TO 60°C.
IDC: SUITABLE FOR 23-26AWG STRANDED AND SOLID WIRE.
MIN. 20-INSTALLATION CYCLES.
PACKAGING:
KIT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE
WITH L-COM PACKAGING SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).



CAT 6, UNSHIELDED
KESTONE ADAPTER
(L-COM P/N: RJSBTL6-RED
WITHOUT PACKAGING)

FLANGE MOUNTED KESTONE ADAPTER

2X 4-40UNC-2A X 1/4" LONG



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

6

5

4

3

2

1

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5]
.XX = ±.02 [0.5]
.XXX = ±.005 [0.13]
FRACTIONS
± 1/32
ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = +1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINIT® brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE
NONE
SHEET
1 OF 1

DESCRIPTION
ETHERNET CATEGORY 6 ULTRA SHORT-BODY TOOL-LESS IDC
KESTONE JACK PANEL MOUNT FLANGE STYLE KIT, RJ45,
UNSHIELDED, RED

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DMAY	ECFRJSBTL6-RED	A