

6

5

4

3

2

1

## REVISION

| ZONE | REV | DESCRIPTION     | DATE       | CHANGED BY | APPROVED    |
|------|-----|-----------------|------------|------------|-------------|
|      | A   | INITIAL RELEASE | 02/13/2026 | DMAY       | DGITTADAURO |

F


E

D

C


B

A




RECOMMENDED  
PANEL OPENING

2X #4-40 UNC-2B



CAT 6A, UNSHIELDED  
KEYSTONE ADAPTER  
(L-COM P/N: RJSBTLC6A-RED  
WITHOUT PACKAGING)



FLANGE MOUNTED KEYSTONE ADAPTER

2X 4-40UNC-2A X 1/4" LONG

## NOTES:

## MATERIAL:

FLANGED ADAPTER: ZINC ALLOY

HARDWARE: STAINLESS STEEL.

## FINISH:

FLANGED ADAPTER: NICKEL PLATE.

## MISCELLANEOUS:

OPERATING TEMPERATURE: -10°C TO 60°C.

IDC: SUITABLE FOR 23-26AWG STRANDED AND SOLID WIRE.

MIN. 20-INSTALLATION CYCLES.

## PACKAGING:

KIT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE  
WITH L-COM PACKAGING SPECIFICATION PS-0031.

## REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
X = ±.2 [5]  
XX = ±.02 [0.5]  
XXX = ±.005 [0.13]  
FRACTIONS  
± 1/32  
ANGLES ± 1°

CABLE LENGTH TOLERANCES:  
≤12 [305] = +1 [25] / -0  
>12 [305] ≤ 60 [1524] = +2 [51] / -0  
>60 [1524] ≤ 120 [3048] = +4 [102] / -0  
>120 [3048] ≤ 300 [7620] = +6 [152] / -0  
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE.  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINIT® brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE  
NONE  
SHEET  
1 OF 1

DESCRIPTION  
ETHERNET CATEGORY 6A/7 10gig ULTRA SHORT-BODY TOOL-  
LESS IDC KEYSTONE JACK PANEL MOUNT FLANGE STYLE KIT,  
RJ45, UNSHIELDED, RED

| SIZE | CAGE CODE | DRAWN BY | ITEM NO.         | REV |
|------|-----------|----------|------------------|-----|
| A    | 43321     | DMAY     | ECFRJSBTLC6A-RED | A   |

6

5

4

3

2

1