


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/09/2023	HBAKKE	PHOSPODAR



ITEM NUMBER	LENGTH	
	METERS	FEET
FCA-FCFC-DPLCV-01	1.0	3.28
FCA-FCFC-DPLCV-05	5.0	16.40

NOTES:

1. CONNECTOR ASSEMBLY POLISH TYPE: PC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-com an INFINIT brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY HBAKKE	08/09/2023		
	CHECKED BY DMAY	08/09/2023		
OVERALL CABLE LENGTH TOLERANCE: $\leq 12 [305] = +1 [25] / -0$ >math>12 [305] \leq 60 [1524] = +2 [51] / -0</math> >math>60 [1524] \leq 120 [3048] = +4 [102] / -0</math> >math>120 [3048] \leq 300 [7620] = +6 [152] / -0</math> >math>300 [7620] = +5\% / -0</math>	APPROVED BY TCAHALANE	08/09/2023		
ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2 [5]$ $.XX = \pm .02 [5]$ $.XXX = \pm .005 [1.3]$	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION	FIBER OPTIC PATCH CABLE FC/PC-FC/PC DUPLEX 100/140 LARGE CORE MULTIMODE FIBER 3.0MM PVC	
THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. FCA-FCFC-DPLCV
		REV. A	SCALE: NONE	CAD FILE: FCA-FCFC-DPLCV.SLDDRW
				SHEET 1 OF 1