


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	08/10/2023	BPUCHASKI	PHOSPODAR


ADAPTER KIT INCLUDES:

1. P ADAPTER HOUSING, BULKHEAD
2. IP LC INNER ADAPTER, FEMALE
3. IP ADAPTER INSERT RETAINER
4. POWER CONTACT MALE PIN 12 AWG
5. IP ADAPTER COMPRESSION SEAL
6. IP ADAPTER NUT
7. IP ADAPTER DUST CAP



NOTES:

1. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031
- REGULATORY COMPLIANCE:  
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div>L-com™</div> <div>an INFINIT® brand</div>		50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]                      FRACTIONS .XX = ± .02 [.5]                ± 1/32 .XXX = ± .005 [.13]            ANGLES ± 1°		DRAWN BY BPUCHASKI		08/10/2023		CATEGORY  FIBER OPTICS		PRODUCT DESCRIPTION IP68 HYBRID LC ADAPTER, SOCKETS (FEMALE) WITH DUST CAP	
		CHECKED BY REVANGELIS		08/10/2023					
		APPROVED BY PHOSPODAR		08/10/2023					
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321		ITEM NO. FOA-LCHBS-D	
				SCALE: NONE		CAD FILE: FOA-LCHBS-D.SLDDRW		SHEET 1 OF 1	