



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 10800: ADDED VALUES -01D, -02D, -03D, -07D, -12D, -18D	11/04/2020	PHOSPODAR



MODEL	ATTENUATION	BACK REFLECTION
FOATSCU-01D	1dB	≤ -55dB
FOATSCU-02D	2dB	≤ -55dB
FOATSCU-03D	3dB	≤ -55dB
FOATSCU-05D	5dB	≤ -55dB
FOATSCU-07D	7dB	≤ -55dB
FOATSCU-10D	10dB	≤ -55dB
FOATSCU-012D	12dB	≤ -55dB
FOATSCU-15D	15dB	≤ -55dB
FOATSCU-18D	18dB	≤ -55dB
FOATSCU-20D	20dB	≤ -55dB
FOATSCU-25D	25dB	≤ -55dB

- NOTES:**
- ATTENUATOR UTILIZES "UPC" POLISH.
 - OPERATING TEMPERATURE RANGE: -40° C TO +75° C.
 - SINGLE MODE WAVELENGTH RANGE: 1310-1550 nm.
 - ATTENUATOR IS PACKAGED TWO WITH DUST CAPS INSTALLED (NOT SHOWN).
 - ATTENUATOR SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY DFRISIELLO CHECKED BY D.CASTRO APPROVED BY P.MC NEIL	DATE 10/29/2007 10/29/2007 10/29/2007	 an INFINITO brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY FIBER OPTICS	PRODUCT DESCRIPTION FIBER SCU ATTENUATOR	SIZE A	CAGE CODE 43321	ITEM NO. FOATSCU
THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: FOATSCU.SLDDRW	SHEET 1 OF 1		