


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/07/2021	PHOSPODAR



SPECIFICATIONS		
WAVELENGTH (nm)	1310±40 & 1550±40	
MODE	G657A2	
ATTENUATOR (dB)	1 - 60	
ACCURACY (dB)	0.02	
RETURN LOSS (dB)	≥60dB (SM/APC) ≥50dB (SM/PC)	
CABLE	OD (mm)	3.0
	MATERIAL	LSZH
	FLAME RESISTANCE	NOT COMPLIANT
TEMPERATURE RANGE	STORAGE OR TRANSPORTATION	-40° C ~ +85° C
	OPERATION	0 ~ +70° C
PDL (dB)	≤0.15	

NOTES:

1. ST CONNECTOR ASSEMBLY POLISH TYPE: UPC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13]	APPROVALS DRAWN BY DFRISIELLO CHECKED BY PHOSPODAR APPROVED BY PHOSPODAR	DATE 05/07/2021 05/07/2021 05/07/2021	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY FIBER OPTICS
SIZE A		CAGE CODE 43321	ITEM NO. FOAV-STU0160-MD0103
SCALE: NONE		CAD FILE: FOAV-STU0160-MD0103.SLDDRW	SHEET 1 OF 1