





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |            |           |
|-----------|-----------------|------------|-----------|
| REV       | DESCRIPTION     | DATE       | APPROVED  |
| A         | INITIAL RELEASE | 03/05/2021 | PHOSPODAR |
|           |                 |            |           |
|           |                 |            |           |



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. CONNECTOR INCLUDES A DUST CAP (NOT SHOWN).
3. CONNECTOR ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

|  |  |  |   |
|--|--|--|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]<br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0<br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2 [5]      FRACTIONS ± 1/32<br>.XX = ± .02 [.5]      ANGLES ± 1°<br>.XXX = ± .005 [.13] | APPROVALS  | DATE   |  50 High Street, West Mill,<br>North Andover, MA 01845 USA.<br>Phone: 1.800.341.5266<br>1.978.682.6936 |
|  | DRAWN BY<br>DZINN<br>CHECKED BY<br>DFRISIELLO<br>APPROVED BY<br>PHOSPODAR              | 03/05/2021<br>03/05/2021<br>03/05/2021   |   |
| THIRD-ANGLE PROJECTION<br>  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY<br>COLOR VARIATIONS MAY OCCUR | PRODUCT DESCRIPTION<br><b>FIBER CONNECTOR, MPO FEMALE, 12 FIBER, FOR 4.0MM MMF, VIOLET, SHORT BOOT, LOW-LOSS</b> | SIZE<br><b>A</b>  |
| CAGE CODE<br><b>43321</b>  |  | ITEM NO.<br><b>FOC-MPFMM1230-VISPO</b>   | REV.<br><b>A</b>  |
| SCALE: NONE  |  | CAD FILE: FOC-MPFMM1230-VISPO.SLDDRW   | SHEET 1 OF 1  |