


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/18/2022	PHOSPODAR



MINI-IP CONNECTOR HOUSING
SC/APC CONNECTOR

MINI-IP CONNECTOR HOUSING
SC/APC CONNECTOR

5mm G657A2 SIMPLEX,
LSZH, BLACK

LENGTH

SHRINK TUBE,
BLACK W/GLUE

MINI-IP (SC/APC)
DUST COVER W/LANYARD



ITEM NO.	LENGTH	
	METER	FEET
FOCB043015N01M	1.0	3.28
FOCB043015N02M	2.0	6.56
FOCB043015N05M	5.0	16.40
FOCB043015N10M	10.0	32.81
FOCB043015N15M	15.0	49.21

NOTES:

1. SC CONNECTOR POLISH TYPE: APC.
2. MINI-IP HOUSING COMES WITH DUST COVER INSTALLED.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY DZINN CHECKED BY DFRISIELLO APPROVED BY PHOSPODAR	DATE 01/18/2022 01/18/2022 01/18/2022	 an INFINITO® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	CATEGORY FIBER OPTIC
		SIZE A	CAGE CODE 43321	ITEM NO. FOCB043015N
		SCALE: NONE	CAD FILE: FOCB043015N.SLDDRW	SHEET 1 OF 1