


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/22/04	MCCORMICK



PART NUMBER	LENGTH METERS
FODFC50-ST-01	1.0
FODFC50-ST-02	2.0
FODFC50-ST-03	3.0
FODFC50-ST-04	4.0
FODFC50-ST-05	5.0

NOTES:  
 1. CONNECTOR ASSEMBLY USES A PC POLISH.  
 2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP (NOT SHOWN).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:  
 .X ±.1  
 .XX ±.05  
 .XXX ±.005  
 CABLE LENGTH TOLERANCE  
 <300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	01/07/2004
CHECKED BY D.PARHAM	01/07/2004
APPROVED BY R.CARRICK	01/07/2004

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

<b>L-com</b> CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION FC TO ST 50/125 DUPLEX			
DRAWING TITLE <b>OUTLINE DRAWING</b>			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. FODFC50-ST-01-OD1	REV. <b>A</b>
SCALE: NONE		CAD FILE: FODFC50-ST-01-OD1.SLDRW	SHEET 1 OF 1