


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

**RoHS Compliant** ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/2/07	C.BERUBE
B	ECN2834 ADDED COLOR CODING	04/27/07	C.BERUBE
B	ECN99999: REMOVED COLOR CODE, DELETED DUST CAP DETAILS	11/05/08	DFP
C	ECN3716: CABLE WAS LISTED AS SINGLEMODE	11/19/08	DFP



PART#	METERS	FEET
FODLC50-CL-01	1	3.3
FODLC50-CL-02	2	6.6
FODLC50-CL-03	3	9.8
FODLC50-CL-04	4	13.1
FODLC50-CL-05	5	16.4
FODLC50-CL-10	10	32.8

**NOTES:**

**CABLE CHARACTERISTICS:**  
 50/125 MULTIMODE DUPLEX FIBER ZIPCORD  
 OFNR JACKET, COLOR: ORANGE  
 CABLE O.D: 3.0 mm

**MISCELLANEOUS:**  
 CABLE ASSEMBLY TO SHIP WITH DUST CAPS INSTALLED. (NOT SHOWN)  
 CABLE ASSEMBLY TO SHIP INDIVIDUALLY IN A POLYBAG

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +5% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15  PROJECTION 	APPROVALS C.BERUBE	DATE 03/28/07		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CHECKED BY J.ROBERTS	DATE 03/29/07			CATEGORY FIBER OPTICS
	APPROVED BY J.ROBERTS	DATE 03/29/07	PRODUCT DESCRIPTION CA LC-LC CLIPPED 50/125		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. FODLC50-CL
REF	SCALE: NONE	CAD FILE: FODLC50-CL.SLDDRW	REV. <b>C</b>	SHEET 1 OF 1	