


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

**RoHS Compliant** ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/29/07	C.BERUBE
B	ECN#2834 ADDED COLOR CODING	04/27/07	C.BERUBE
B	ECN99999: ADDED SUBCABLE COLORS TO NOTES. DEL DUST CAP DETAILS	11/05/08	DFP



PART#	METERS	FEET
FODLC50-UNI-01	1	3.3
FODLC50-UNI-02	2	6.6
FODLC50-UNI-03	3	9.8
FODLC50-UNI-04	4	13.1
FODLC50-UNI-05	5	16.4
FODLC50-UNI-10	10	32.8

**NOTES:**

**CABLE CHARACTERISTICS:**  
 50/125 DUPLEX FIBER (SINGLE JACKET)  
 OFNR JACKET, COLOR: ORANGE  
 SUBCABLE JACKET COLORS: BLUE, ORANGE  
 CABLE O.D.: 3mm

**MISCELLANEOUS:**  
 CABLE ASSEMBLY TO SHIP WITH DUST CAPS INSTALLED (NOT SHOWN)  
 CABLE ASSEMBLY TO SHIP INDIVIDUALLY IN A POLYBAG

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2[51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 / -0 $>120$ [3048] $\leq 300$ [7620] = +6 / -0 $>300$ [7620] = +5% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15	APPROVALS DRAWN BY C.BERUBE	DATE 03/29/07	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	CHECKED BY J.ROBERTS	DATE 03/29/07		CATEGORY FIBER OPTICS		
	APPROVED BY J.ROBERTS	DATE 03/29/07	PRODUCT DESCRIPTION LC-LC 50/125 DUPLEX ASSEMBLY			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. FODLC50-UNI
SCALE: NONE		CAD FILE: FODLC50-UNI.SLDDRW		SHEET 1 OF 1		