



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED TO PRODUCTION	8/18/2000	R.CARRICK
B	ADDED LENGTHS TO CHART. CHANGED O.D TO 3.0MM SEE ECN #0792	11/29/00	R.CARRICK
C	REVISED TABLE ECN# 1128	05/30/02	MCCORMICK
D	REVISED CABLE MARKERS (ECN 1274)	12/31/02	MCCORMICK



PART NUMBER	LENGTH	
	METERS	FEET
FODSC50-01	1.0	3.3
FODSC50-02	2.0	6.6
FODSC50-03	3.0	9.8
FODSC50-04	4.0	13.1
FODSC50-05	5.0	16.4
FODSC50-10	10.0	32.8
FODSC50-15	15.0	49.2
FODSC50-20	20.0	65.6
FODSC50-25	25.0	82.0
FODSC50-30	30.0	98.4
FODSC50-35	35.0	114.8
FODSC50-40	40.0	131.2
FODSC50-45	45.0	147.6
FODSC50-50	50.0	164.0
FODSC50-75	75.0	246.1
FODSC50-100	100.0	328.1
FODSC50-125	125.0	410.1
FODSC50-150	150.0	492.1



- NOTES:
 1. CONNECTOR ASSEMBLY USES A PC POLISH.
 2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP (NOT SHOWN).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:
 .X ±.1
 .XX ±.05
 .XXX ±.005
 CABLE LENGTH TOLERANCE
 <300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY RON CARRICK	8/16/2000
CHECKED BY	
ENG	8/16/2000
APPROVED BY AFC	8/18/2000

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

L-com
 CONNECTIVITY PRODUCTS
 45 BEECHWOOD DRIVE
 NORTH ANDOVER, MA
 01845

PRODUCT DESCRIPTION
50/125 MULTIMODE FIBER

DRAWING TITLE
OUTLINE DRAWING

SIZE	FSCM NO.	DWG. NO.	REV.
A	43321	FODSC50-01-OD1	D
SCALE: 1:1	CAD FILE: FODSC50-01-OD1.SLDDRW		SHEET 1 OF 1