


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED TO PRODUCTION	8/18/2000	R.CARRICK
B	ADDED LENGTHS TO CHART. CHANGED O.D TO 3.0MM SEE ECN #0792	11/29/00	R.CARRICK
C	REVISED CABLE MARKING [ECN 1274]	01/02/03	MCCORMICK



PART NUMBER	LENGTH	
	METERS	FEET
FODSTC50-01	1.0	3.3
FODSTC50-02	2.0	6.6
FODSTC50-03	3.0	9.8
FODSTC50-04	4.0	13.1
FODSTC50-05	5.0	16.4
FODSTC50-10	10.0	32.8
FODSTC50-15	15.0	49.2
FODSTC50-20	20.0	65.6
FODSTC50-25	25.0	82.0
FODSTC50-30	30.0	98.4
FODSTC50-35	35.0	114.8
FODSTC50-40	40.0	131.2
FODSTC50-45	45.0	147.6
FODSTC50-50	50.0	164.0
FODSTC50-75	75	246.1
FODSTC50-100	100	328.1
FODSTC50-125	125	410.1
FODSTC50-150	150	492.1

- NOTES:  
 1. CONNECTOR ASSEMBLY USES PC POLISH.  
 2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP (NOT SHOWN).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:  
 .X ±.1  
 .XX ±.05  
 .XXX ±.005  
 CABLE LENGTH TOLERANCE  
 <300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY RON CARRICK	8/16/2000
CHECKED BY ENG	8/16/2000
APPROVED BY AFC	8/18/2000

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

**L-com**  
 CONNECTIVITY PRODUCTS  
 45 BEECHWOOD DRIVE  
 NORTH ANDOVER, MA  
 01845

PRODUCT DESCRIPTION  
**50/125 MULTIMODE FIBER**

DRAWING TITLE  
**OUTLINE DRAWING**

SIZE **A** FSCM NO. **43321** DWG. NO. **FODSTC50-01-OD1** REV. **C**

SCALE: 1:1 CAD FILE: FODSTC50-01-OD1.SLDRW SHEET 1 OF 1