



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/08/04	MCCORMICK
B	ECN# 2325 ADDED NOTES	03/08/06	MCCORMICK
C	ECN# 2535; REMOVED OFNP FROM CABLE DESCRIPTION	08/22/06	MCCORMICK



PART	LENGTH METERS
FODZFC50-01	1.0
FODZFC50-02	2.0
FODZFC50-03	3.0
FODZFC50-04	4.0
FODZFC50-05	5.0

NOTES:

- 1.0 **TEST:**
1.1 INSERTION LOSS TESTED AT 1300nm WITH A <-1.0 dB RESULT.
- 2.0 **MANUFACTURING:**
2.1 CABLE ASSEMBLY UTILIZES "PC" POLISH TYPE.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:
 X ±.1
 XX ±.05
 XXX ±.005
 CABLE LENGTH TOLERANCE
 <300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	11/08/2004
CHECKED BY D.PARHAM	11/08/2004
APPROVED BY R.CARRICK	11/08/2004

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

L-com 45 BEECHWOOD DRIVE
 CONNECTIVITY PRODUCTS NORTH ANDOVER, MA 01845

PRODUCT DESCRIPTION
50/125 DUPLEX LSZH CABLE ASSY

DRAWING TITLE
OUTLINE DRAWING

SIZE A	FSCM NO. 43321	DWG. NO. FODZFC50-01-OD1	REV. C
------------------	--------------------------	------------------------------------	------------------

SCALE: NONE | CAD FILE: FODZFC50-01-OD1.SLDDRW | SHEET 1 OF 1