


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN# 2325; ADDED NOTES	03/08/06	MCCORMICK
C	ECN# 2535; REMOVED OFNP FROM CABLE DESCRIPTION	08/22/06	MCCORMICK
D	ECN# 2641; CABLE WAS 1AL06-074, REVISED FORMAT & TOLERANCE	12/05/06	MCCORMICK
D	ECN99999; ADDED END VIEWS AND NOTE 3. UPDATED FORMAT.	02/08/10	DFP



PART #	LENGTH FEET [METERS]
FODZMTRJ50-01	3.28 [1.0]
FODZMTRJ50-02	6.56 [2.0]
FODZMTRJ50-03	9.84 [3.0]
FODZMTRJ50-04	13.12 [4.0]
FODZMTRJ50-05	16.40 [5.0]

NOTES:

- CONNECTOR ASSEMBLY USES A PC POLISH.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY C.MCCORMICK	12/03/2002				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D.PARHAM	12/03/2002	CATEGORY FIBER OPTIC			
	APPROVED BY R.CARRICK	12/03/2002	PRODUCT DESCRIPTION 50/125 MTRJ LSZH CABLE ASSY			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. FODZMTRJ50	REV. D
			SCALE: NONE	CAD FILE: FODZMTRJ50.SLDDRW	SHEET 1 OF 1	