



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/08/04	MCCORMICK
B	ECN# 2325 ADDED NOTES	03/08/06	MCCORMICK
C	ECN# 2535; REMOVED OFNP FROM CABLE DESCRIPTION	08/22/06	MCCORMICK



PART #	LENGTH METERS
FODZSC50-01	1.0
FODZSC50-02	2.0
FODZSC50-03	3.0
FODZSC50-04	4.0
FODZSC50-05	5.0

NOTES:

- 1.0 **TEST:**
 - 1.1 INSERTION LOSS TESTED AT 1300nm WITH A <-1.0 dB RESULT.
- 2.0 **MANUFACTURING:**
 - 2.1 CABLE ASSEMBLY UTILIZES "PC" POLISH TYPE.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:
 X ±.1
 XX ±.05
 XXX ±.005
 CABLE LENGTH TOLERANCE
 ≤300' ±5% >300' ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	11/08/2004
CHECKED BY D.PARHAM	11/08/2004
APPROVED BY R.CARRICK	11/08/2004

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION 50/125 DUPLEX LSZH CABLE ASSY			
DRAWING TITLE OUTLINE DRAWING			
SIZE A	FSCM NO. 43321	DWG. NO. FODZSC50-01-OD1	REV. C
SCALE: NONE		CAD FILE: FODZSC50-01-OD1.SLDDRW	SHEET 1 OF 1