


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/08/04	MCCORMICK
B	ECN# 2325 ADDED NOTES	03/08/06	MCCORMICK
C	ECN# 2535; REMOVED OFNP FROM CABLE DESCRIPTION	08/22/06	MCCORMICK



PART #	LENGTH METERS
FODZST50-01	1.0
FODZST50-02	2.0
FODZST50-03	3.0
FODZST50-04	4.0
FODZST50-05	5.0

**NOTES:**

- 1.0 **TEST:**
  - 1.1 INSERTION LOSS TESTED AT 1300nm WITH A <-1.0 dB RESULT.
- 2.0 **MANUFACTURING:**
  - 2.1 CABLE ASSEMBLY UTILIZES "PC" POLISH TYPE.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:  
 X ±.1  
 XX ±.05  
 XXX ±.005  
 CABLE LENGTH TOLERANCE  
 <300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	11/08/2004
CHECKED BY D.PARHAM	11/08/2004
APPROVED BY R.CARRICK	11/08/2004

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

<b>L-com</b> CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION <b>50/125 DUPLEX LSZH CABLE ASSY</b>			
DRAWING TITLE <b>OUTLINE DRAWING</b>			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>FODZST50-01-OD1</b>	REV. <b>C</b>
SCALE: NONE		CAD FILE: FODZST50-01-OD1.SLDDRW	SHEET 1 OF 1