

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/17/12	D.GRIFFIN




CHART A								
FPT9OM2-SC-12PK-1			FPT9OM2-SC-12PK-2			FPT9OM2-SC-12PK-3		
PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR
FPT9OM2-SC-BLK-1	1.0 [3.28]	BLACK	FPT9OM2-S-C-BLK-2	2.0 [6.56]	BLACK	FPT9OM2-S-C-BLK-3	3.0 [9.84]	BLACK
FPT9OM2-SC-ORG-1	1.0 [3.28]	ORANGE	FPT9OM2-S-C-ORG-2	2.0 [6.56]	ORANGE	FPT9OM2-S-C-ORG-3	3.0 [9.84]	ORANGE
FPT9OM2-SC-YLW-1	1.0 [3.28]	YELLOW	FPT9OM2-S-C-YLW-2	2.0 [6.56]	YELLOW	FPT9OM2-S-C-YLW-3	3.0 [9.84]	YELLOW
FPT9OM2-SC-GRY-1	1.0 [3.28]	GRAY	FPT9OM2-S-C-GRY-2	2.0 [6.56]	GRAY	FPT9OM2-S-C-GRY-3	3.0 [9.84]	GRAY
FPT9OM2-SC-BLU-1	1.0 [3.28]	BLUE	FPT9OM2-S-C-BLU-2	2.0 [6.56]	BLUE	FPT9OM2-S-C-BLU-3	3.0 [9.84]	BLUE
FPT9OM2-SC-GRN-1	1.0 [3.28]	GREEN	FPT9OM2-S-C-GRN-2	2.0 [6.56]	GREEN	FPT9OM2-S-C-GRN-3	3.0 [9.84]	GREEN
FPT9OM2-SC-AQU-1	1.0 [3.28]	AQUA	FPT9OM2-S-C-AQU-2	2.0 [6.56]	AQUA	FPT9OM2-S-C-AQU-3	3.0 [9.84]	AQUA
FPT9OM2-SC-BRN-1	1.0 [3.28]	BROWN	FPT9OM2-S-C-BRN-2	2.0 [6.56]	BROWN	FPT9OM2-S-C-BRN-3	3.0 [9.84]	BROWN
FPT9OM2-SC-RED-1	1.0 [3.28]	RED	FPT9OM2-S-C-RED-2	2.0 [6.56]	RED	FPT9OM2-S-C-RED-3	3.0 [9.84]	RED
FPT9OM2-SC-WHT-1	1.0 [3.28]	WHITE	FPT9OM2-S-C-WHT-2	2.0 [6.56]	WHITE	FPT9OM2-S-C-WHT-3	3.0 [9.84]	WHITE
FPT9OM2-SC-VIO-1	1.0 [3.28]	VIOLET	FPT9OM2-S-C-VIO-2	2.0 [6.56]	VIOLET	FPT9OM2-S-C-VIO-3	3.0 [9.84]	VIOLET
FPT9OM2-SC-ROS-1	1.0 [3.28]	ROSE	FPT9OM2-S-C-ROS-2	2.0 [6.56]	ROSE	FPT9OM2-S-C-ROS-3	3.0 [9.84]	ROSE

NOTES:

1. SC CONNECTOR ASSEMBLY POLISH TYPE: PC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE PACKAGED 12 PIECES PER BAG IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY D.PARHAM CHECKED BY D.GUITADAURO APPROVED BY D.GALLAGHER	DATE 05/11/2012 05/15/2012 07/13/2012		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CATEGORY FIBER OPTIC			PRODUCT DESCRIPTION SC OM2 SMLPX 900µm OFNR	
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321
	DWG. NO. FPT9OM2-SC-12PK		SCALE: NONE	CAD FILE: FPT9OM2-SC-12PK.SLDDRW	SHEET 1 OF 1