





| PART NO.  | LENGTH                | TOL in [mm]                |
|-----------|-----------------------|----------------------------|
| HD1428-25 | 25 FEET [7.6 METERS]  | +5.98 / -2.00 [+152 / -51] |
| HD1428-50 | 50 FEET [15.2 METERS] | +5.98 / -2.00 [+152 / -51] |
| HD1428-75 | 75 FEET [22.9 METERS] | +5.98 / -2.00 [+152 / -51] |


NOTES:

1. CABLE:  
UL20276 HDMI1.4 CABLE, (28# \* 1P + D + MYLAR + AL) \* 5P + 28AWG \*4C + AEB(AL.) JACKET: BLACK, OD .287 +0/-0.006 [7.3 +0/-0.15].
2. CONNECTOR P1 & P2: HDMI 19P MALE, GOLD PLATED CONTACTS,  
GOLD PLATED SHELL, PBT BLACK
3. HDMI CABLE IS VERSION 1.4 AND SUPPORT 1080P RESOLUTION.
4. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
5. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

| REVISION |     |                 |          |            |          |
|----------|-----|-----------------|----------|------------|----------|
| ZONE     | REV | DESCRIPTION     | DATE     | CHANGED BY | APPROVED |
|          | A   | INITIAL RELEASE | 7/8/2025 | KDANG      | DGUST    |



|                                                                                                                                                                                                               |           |                                                                                                     |          |                                                                                                  |                 |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|-----------------------------------------------------------------------------------------------------|----------|--------------------------------------------------------------------------------------------------|-----------------|
| UNLESS OTHERWISE SPECIFIED<br>LEADING DIMENSIONS ARE INCHES<br>DIMENSIONS IN [ ] ARE MILLIMETERS                                                                                                              |           | <div>L-com®</div> <div>an INFINITE® brand</div>                                                     |          | <div></div> |                 |
| TOLERANCES:                                                                                                                                                                                                   |           | Website: <a href="http://www.L-com.com">www.L-com.com</a><br>Phone: 1.800.341.5266   1.978.682.6936 |          | INTERPRET ALL DIMENSIONS AND<br>TOLERANCES PER ASME Y14.5                                        |                 |
| X = ±2 [5]      FRACTIONS<br>XX = ±.02 [0.5]      ± 1/32<br>XXX = ±.005 [0.13]      ANGLES ± 1°                                                                                                               |           |                                                                                                     |          | SCALE<br>NONE                                                                                    | SHEET<br>1 OF 1 |
| CABLE LENGTH TOLERANCES:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤ 60 [1524] = +2 [51] / -0<br>>60 [1524] ≤ 120 [3048] = +4 [102] / -0<br>>120 [3048] ≤ 300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0 |           | DESCRIPTION<br><br>HIGH SPEED HDMI CABLE, 4K@30HZ RESOLUTION, MALE TO MALE, 28 AWG                  |          |                                                                                                  |                 |
| ALL DIMENSIONS ARE FOR REFERENCE ONLY<br>AND SUBJECT TO CHANGE WITHOUT NOTICE.<br>UN-DIMENSIONED/NON-CRITICAL FEATURES<br>MAY VARY IN SIZE AND LOCATION<br>COLORS MAY VARY                                    |           |                                                                                                     |          |                                                                                                  |                 |
| SIZE                                                                                                                                                                                                          | CAGE CODE | DRAWN BY                                                                                            | ITEM NO. | REV                                                                                              |                 |
| A                                                                                                                                                                                                             | 43321     | KDANG                                                                                               | HD1428   | A                                                                                                |                 |