

6

5

4

3

2

1

REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	7/8/2025	KDANG	DGUST

F


E

D

C


B

A



PART NO.	LENGTH	TOL in [mm]
HD4K26-35	35 FEET [10.7 METERS]	+5.98 / -2.00 [+152 / -51]
HD4K26-40	40 FEET [12.2 METERS]	+5.98 / -2.00 [+152 / -51]
HD4K26-45	45 FEET [13.7 METERS]	+5.98 / -2.00 [+152 / -51]
HD4K26-50	50 FEET [15.2 METERS]	+5.98 / -2.00 [+152 / -51]
HD4K26-60	60 FEET [18.3 METERS]	+5.98 / -2.00 [+152 / -51]

WIRE CONNECTION



NOTES:

- CABLE:
UL20276 ULTRA HIGH SPEED A/V CABLE (26AWG * 2C + AL + D + HM) * 4P + (31AWG * 1P + D + AL + HM) * 1C + 30AWG * 4C + 26AWG * 1C + F + MY + ADB16/11/0.12AL JACKET: BLACK, OD .287 +0/-0.008 [7.3 +0/-0.2].
- CONNECTOR P1 & P2: HDMI 19P MALE, GOLD PLATED CONTACTS, GOLD PLATED SHELL, PBT BLACK
- SUPPORT FOR 4K/60Hz, HDCP2.2 4:4:4 DP1.2
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
TOLERANCES:	
X = ±.2 [5]	FRACTIONS ± 1/32
.XX = ±.02 [0.5]	ANGLES ± 1°
.XXX = ±.005 [0.13]	
CABLE LENGTH TOLERANCES:	
≤12 [305] = +1 [25] / -0	
>12 [305] ≤ 60 [1524] = +2 [51] / -0	
>60 [1524] ≤ 120 [3048] = +4 [102] / -0	
>120 [3048] ≤ 300 [7620] = +6 [152] / -0	
>300 [7620] = +5% / -0	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UN-DIMENSIONED NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY	

L-com
an INFINIT® brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE	SHEET
NONE	1 OF 1

DESCRIPTION

HIGH SPEED HDMI CABLE, 4K@60HZ RESOLUTION, MALE TO MALE, 26 AWG

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	KDANG	HD4K26	A

6

5

4

3

2

1