

6

5

4

3

2

1

## REVISION

| ZONE | REV | DESCRIPTION     | DATE       | CHANGED BY | APPROVED  |
|------|-----|-----------------|------------|------------|-----------|
|      | A   | INITIAL RELEASE | 06/13/2024 | HBAKKE     | THOUGHTON |

F

F

E

E

D

D

C


C

B

B

A

A



| ITEM NUMBER      | DESCRIPTION                                       | LENGTH (FT) | WIDTH (IN) | COLOR |
|------------------|---|-------------|------------|-------|
| LC-HLR050BLK-15F | 1/2 INCH ROLL HOOK & LOOP CABLE TIES - 15FT BLACK | 15          | .50        | BLACK |
| LC-HLR050BLK-33F | 1/2 INCH ROLL HOOK & LOOP CABLE TIES - 33FT BLACK | 33          | .50        | BLACK |
| LC-HLR050BLK-82F | 1/2 INCH ROLL HOOK & LOOP CABLE TIES - 82FT BLACK | 82          | .50        | BLACK |
| LC-HLR075BLK-15F | 3/4 INCH ROLL HOOK & LOOP CABLE TIES - 15FT BLACK | 15          | .75        | BLACK |
| LC-HLR075BLK-33F | 3/4 INCH ROLL HOOK & LOOP CABLE TIES - 33FT BLACK | 33          | .75        | BLACK |
| LC-HLR075BLK-82F | 3/4 INCH ROLL HOOK & LOOP CABLE TIES - 82FT BLACK | 82          | .75        | BLACK |
| LC-HLR100BLK-15F | 1 INCH ROLL HOOK & LOOP CABLE TIES - 15FT BLACK   | 15          | 1          | BLACK |
| LC-HLR100BLK-33F | 1 INCH ROLL HOOK & LOOP CABLE TIES - 33FT BLACK   | 33          | 1          | BLACK |
| LC-HLR100BLK-82F | 1 INCH ROLL HOOK & LOOP CABLE TIES - 82FT BLACK   | 82          | 1          | BLACK |

## NOTES:

- ALL LENGTHS LISTED ARE APPROXIMATE.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS


TOLERANCES:  
 .X = ±.2 [5]      FRACTIONS  
 .XX = ±.02 [0.5]      ± 1/32  
 .XXX = ±.005 [0.13]      ANGLES ± 1°

CABLE LENGTH TOLERANCES:  
 ≤12 [305] = +1 [25] / -0  
 >12 [305] ≤ 60 [1524] = +2 [51] / -0  
 >60 [1524] ≤ 120 [3048] = +4 [102] / -0  
 >120 [3048] ≤ 300 [7620] = +6 [152] / -0  
 >300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE.  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**<sup>®</sup>  
an INFINIT<sup>®</sup> brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

|       |        |
|-------|--------|
| SCALE | SHEET  |
| NONE  | 1 OF 1 |

## DESCRIPTION

1 INCH ROLL HOOK & LOOP CABLE TIES - 82FT BLACK

| SIZE | CAGE CODE | DRAWN BY | ITEM NO.         | REV |
|------|-----------|----------|------------------|-----|
| A    | 43321     | HBAKKE   | LC-HLR100BLK-82F | A   |

6

5

4

3

2

1