


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISION | | | | | |
|----------|------|-----------------|------------|------------|-------------|
| ZONE | REV. | DESCRIPTION | DATE | CHANGED BY | APPROVED BY |
| | A | INITIAL RELEASE | 06/23/2023 | VTHANGARAJ | AGANWANI |



NOTES:

- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
- CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

| | | | | | |
|---|--|---|--|----------------------------------|----------------------|
| <p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5] FRACTIONS $\pm 1/32$.XX = $\pm .02$ [.5] ANGLES $\pm 1^\circ$.XXX = $\pm .005$ [.13]</p> <p>THIRD-ANGLE PROJECTION</p> | <p>APPROVALS</p> <p>DATE</p> | <p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p> | | | |
| | <p>DRAWN BY VTHANGARAJ</p> <p>CHECKED BY KLEITLEIN</p> <p>APPROVED BY AGANWANI</p> | | <p>06/23/2023</p> <p>06/23/2023</p> <p>06/23/2023</p> | | |
| | <p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> | | <p>CATEGORY</p> <p>COAXIAL</p> | | |
| | <p>COLOR VARIATIONS MAY OCCUR</p> | | <p>PRODUCT DESCRIPTION</p> <p>MCX PLUG RIGHT ANGLE TO SMA MALE RIGHT ANGLE CABLE USING RG316-DS COAX WITH HEATSHRINK</p> | | |
| | | <p>SIZE</p> <p>A</p> | <p>CAGE CODE</p> <p>43321</p> | <p>ITEM NO.</p> <p>LCCA31459</p> | <p>REV.</p> <p>A</p> |
| | | <p>SCALE: NONE</p> | <p>CAD FILE: LCCA31459.SLDDRW</p> | <p>SHEET 1 OF 1</p> | |