

6

5

4

3

2

1

F

E

D

C

B

A

F








E

D

C

B

A



NOTES:

1. **QC** IMPORTANT DIMENSION.
2. WATERPROOF RATE: IP67, MATED
3. CONNECTOR: THERMOPLASTIC, BLACK
4. PIN: COPPER ALLOY, GOLD PLATED
5. SHIELD: METAL, NICKEL PLATED
6. NUT: METAL, NICKEL PLATED
7. O-RING: SILICON, GRAY
8. O-RING2: SILICON, GRAY
9. FOR PANEL THICKNESS: 1.0 ~ 4.0mm
10. FOR PCB THICKNESS: 1.6 ~ 2.4mm
11. ASSEMBLE NUT ON CONNECTOR
12. TEMPERATURE RANGE: -40°C TO +105°C
13. OPERATING VOLTAGE: 50V AC / 60V DC
14. RATED CURRENT @40°C: 0.5A
15. COMPONENT SHALL BE INDIVIDUALLY PACKAGED

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

6

5

4

3

2

1