



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/26/10	D.GRIFFIN
B	ECN4691: ADDED M12 CONNECTOR CALL-OUT	04/16/10	D.FP
C	ECN 6206: ADDED "D-CODED" FOR CLARIFICATION, REVISED WIRE MAP	6/1/12	D.FRISIELLO
D	ECN 8875: CHG DIM ON RJ45+BOOT LENGTH TO 41.6mm	8/2/2017	R.CLARK



PART NUMBER	LENGTH	
	FEET	METERS
M12RJ454D-0.5	1.64	0.5
M12RJ454D-1	3.28	1
M12RJ454D-2	6.56	2
M12RJ454D-3	9.84	3
M12RJ454D-5	16.41	5

- NOTE:
1. WATERPROOF RATING: IP68 (P1 ONLY)
 2. MOLDED HOOD/BOOT: POLYURETHANE, BLACK
 3. SCREW NUT: ZINC ALLOY, NICKEL PLATED
 4. PINS/CONTACTS: COPPER ALLOY, GOLD PLATED
 5. CABLE ASSEMBLIES INDIVIDUALLY PACKAGED IN A POLYBAG PER L-COM SPECIFICATION PS-0031.
 6. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
 7. CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM	01/21/2010		CATEGORY TELECOM/MODULAR
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [.51] .XXX = ±.005 [0.13]	CHECKED BY D. CASTRO	01/25/2010	PRODUCT DESCRIPTION CA M12 TO RJ45 4 POS D-CODED	
PROJECTION 	APPROVED BY P. McNEIL	01/25/2010	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SCALE: NONE
	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321
			DWG. NO. M12RJ454D	REV. D
			CAD FILE: M12RJ454D.SLDDRW	
			SHEET 1 OF 1	