


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/17/20	PHOSPODAR

WIRING MAP



PAIR	LC	1X12	REF DES
P1	1	1	J1
	12	12	
P2	2	2	
	11	11	
P3	3	3	
	10	10	
P4	4	4	
	9	9	
P5	5	5	
	8	8	
P6	6	6	
	7	7	



PART NUMBER	METERS (FEET)
MPF12OM3-20LCR-1	1.0 (3.28)
MPF12OM3-20LCR-3	3.0 (9.84)
MPF12OM3-20LCR-5	5.0 (16.40)
MPF12OM3-20LCR-10	10.0 (32.81)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [5]      ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY DFRISIELLO CHECKED BY PHOSPODAR APPROVED BY PHOSPODAR	DATE 11/17/2020 11/17/2020 11/17/2020	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY <b>FIBER OPTICS</b>
SCALE: NONE		CAGE CODE <b>A 43321</b>	ITEM NO. <b>MPF12OM3-20LCR</b>	REV. <b>A</b>
CAD FILE: MPF12OM3-20LCR.SLDDRW			SHEET 1 OF 1	